

Manufacturer SOCOMECSAS
1-4 rue de Westhouse
67230 BENFELD
FRANCE

Product type **Enclosed transfer switching equipment**

Product model(s) **ATyS**

Product references **See next pages**

This declaration of conformity is issued under the sole responsibility of the manufacturer. The above mentioned equipment(s), with respect to the relevant installation, maintenance and use requirements regarding to its (their) destination, regulations, standards and manufacturer instructions, is in conformity with the relevant statutory requirements applicable to the specific product:

2012 No.3032 ***The Restriction of the Use of Certain Hazardous Substances in Electrical and Electronic Equipment Regulations***

2016 No.1101 ***The Electrical Equipment (Safety) Regulations***

2016 No.1091 ***The Electromagnetic Compatibility Regulations***

As amended by:
2019 No. 696 ***The Product Safety and Metrology etc. (Amendment etc.) (EU Exit) Regulations***

References of designated standards applied:

2012 No.3032 **EN IEC 63000: 2018**

2016 No.1101 **EN 61439-2:2012**
EN 60947-6-1:2005/A1:2014

2016 No.1091 **EN 61439-2:2012**
EN 60947-6-1:2005/A1:2014

This declaration shall cease to be valid if any modification is made on the equipment(s).

Date **12/04/2023**

Place **Benfeld**



Alan REED
Power Switching & Monitoring Application Director



ATyS gM Steel enclosure	ATyS pM Steel enclosure	Accessories
18544004 ; 18544005 ; 18544006 ; 18544007 ; 18544008 ; 18544009 ; 18544010 ; 18544011 ; 18544012 ; 18544013 ; 18544016 ; 18544017	18844004 ; 18844005 ; 18844006 ; 18844007 ; 18844008 ; 18844009 ; 18844010 ; 18844011 ; 18844012 ; 18844013 ; 18844016 ; 18844017	Contact auxiliaire 13091001 Solid neutral 13099008 Kit IP54 13994016 Voltage sensing & power supply 13994006 Cage terminal interface 13994017
	18873004 ; 18874004 ; 18873006 ; 18874006 ; 18873008 ; 18874008 ; 18873010 ; 18874010 ; 18873012 ; 18874012 ; 18873016 ; 18874016	
ATyS dM Steel enclosure		Solid neutral 13099008 Kit IP54 13994016
18234004 ; 18234005 ; 18234006 ; 18234007 ; 18234008 ; 18234009 ; 18234010 ; 18234011 ; 18234012 ; 18234013 ; 18234016 ; 18234017		

ATyS S Steel enclosure	Connecting kit
35054004 ; 35054006 ; 35054008 ; 35054010 ; 35054012	95990018
ATyS dS Steel enclosure	
35134004 ; 35134006 ; 35134008 ; 35134010 ; 35134012	

ATyS d Steel enclosure	ATyS r Steel enclosure	ATyS g Steel enclosure	Solid neutral
17234012 17234016			15991006
	87234020	87534020	15991020
17234025	87234025	87534025	15991025
17234040	87234040	87534040	15991040
17234063	87234063	87534063	15991063
17234080	87234080	87534080	15991080
17234100	87234100	87534100	15991100
17234120	87234120	87534120	15991120
17234160	87234160	87534160	15991160
17234200 17234250 17234320	87234200 87234250 87234320	87534200 87534250 87534320	

Product models	Accessories
ATyS M Polymeric enclosure 18554004 ; 18554006 ; 18554008 ; 18554010 ; 18554012 ; 18554016	
ATyS dM Polymeric enclosure 18232004 ; 18232006 ; 18232008 ; 18232010 ; 18232012 ; 18232016	Auxiliary contact 13091001 Voltage sensing & power supply 13994006 Dual power supply 15994001
ATyS gM Polymeric enclosure 18542004 ; 18542006 ; 18542008 ; 18542010 ; 18542012 ; 18542016	Auxiliary contact 13091001 Voltage sensing & power supply 13994006

ATyS p Steel enclosure	Solid neutral	Other accessories
17634012 17634016	15991006	ATyS D10 95992010 ATyS D20 95992020 Cable RJ45 15992009 Communication module RS485 MODBUS 15992000 2 input/2 output module 15992001
17634025	15991025	
17634040	15991040	
17634063	15991063	
17634080	15991080	
17634100	15991100	
17634120	15991120	
17634160	15991160	
17634200 17634250 17634320		
87734020	15991020	
87734025	15991025	
87734040	15991040	
87734063	15991063	
87734080	15991080	
87734100	15991100	
87734120	15991120	
87734160	15991160	
87734200 ; 87734250 ; 87734320		
18873025 ; 18874025 ; 18873040 ; 18874040		

ATyS Bypass	Tinned busbar	Other accessories	2 input/2 output module
17854004 ; 17854006 ; 17854008 ; 17854010 ; 17854012 ; 17864004 ; 17864006 ; 17864008 ; 17864010 ; 17864012		Protection against overvoltage 15999016 Engine exerciser 15999006	
17854016 ; 17864016			
17854025 ; 17864025	15999007	Protection against overvoltage 15999017	15992001
17854040 ; 17864040	15999008		
17854063 ; 17864063	15999009	Protection against overvoltage 15999018	
17854080 ; 17864080	15999010		
17854100 ; 17864100	15999011		
17854120 ; 17864120	15999013	Protection against overvoltage 15999018	
17854160 ; 17864160			
17854200 ; 17864200	15999014	Extension cabinet 15999004	
17854250 ; 17864250	15999015	Protection against overvoltage 15999018	
17854320 ; 17864320		Extension cabinet 15999004	