

Selection guide

Complementary solutions

Back-up storage, Communication and connectivity, Power Distribution Unit (PDU)

p. 89



Ultimate

Power	0.5	1	2	3	5	10	20	50	100	160	200	300	500	1000	4800 kVA
UPS - Modular solutions															
	MODULYS XS	p. 18				2.5 - 20 kVA X/1									
	MODULYS RM GP	p. 22						25 - 75 kVA/kW 3/3 Rack-mounted							
	MODULYS GP	p. 26							25 - 600 kVA/kW 3/3						
	MODULYS XL	p. 32										200 - 4800 kVA/kW 3/3			
STS - Static Transfer System															
	STATYS	p. 36							32 - 1800 A 3/3						



Superior

Power	0.5	1	2	3	5	10	20	50	100	160	200	300	500	1000	4800 kVA
UPS - Single-phase															
	NETYS RT	p. 40			1.1 - 11 kVA 1/1 Convertible Rack/Tower										
	NETYS RT-M	p. 44			1.1 - 3.3 kVA 1/1 - For marine applications										
UPS - Three-phase															
	MASTERYS GP4 RK	p. 46						10 - 40 kVA/kW 3/1 & 3/3 - Rack-mounted							
	MASTERYS GP4	p. 48						10 - 160 kVA/kW 3/1 & 3/3							
	DELPHYS GP	p. 50								160 - 1000 kVA/kW 3/3					
UPS - Transformer-based															
	MASTERYS IP+	p. 52						10 - 80 kVA 3/1 & 3/3							
	DELPHYS MX	p. 54										250 - 900 kVA 3/3			
AC/DC systems															
	SHARYS IP system	p. 56				60 - 200 A 24/48/110 VDC									
STS - Transfer System															
	STATYS XS	p. 60				16 & 32 A 1/1 - Rack-mounted									

Selection guide

Complementary solutions
 Back-up storage, Communication and connectivity,
 Power Distribution Unit (PDU)
 p. 89

Power | 0.5 | 1 | 2 | 3 | 5 | 10 | 20 | 50 | 100 | 160 | 200 | 300 | 500 | 1000 | 4800 kVA



Prime

UPS - Single-phase

	NETYS PL	p. 64	600 - 800 VA 1/1 Desktop																	
	NETYS PE	p. 66	600 - 2000 VA 1/1 - Mini Tower																	
	NETYS PR Mini Tower	p. 68	1 - 2 kVA 1/1 - Mini Tower																	
	NETYS PR Rack/Tower	p. 70	1.7 - 3.3 kVA 1/1 - Convertible Rack/Tower																	
	NETYS PR Rack 1U	p. 72	1 & 1.5 kVA 1/1 19" Rack																	
	ITYS	p. 74	1 - 10 kVA 1/1 & 3/1 - Tower																	
	ITYS ES	p. 76	1 - 3 kVA 1/1 - Tower																	

UPS - Three-phase

	MASTERY BC+ FLEX	p. 78								10 - 40 kVA 3/1 & 3/3 - Free-standing, wall-mounted, top-mounted										
	MASTERY BC+	p. 80								10 - 160 kVA 3/1 & 3/3										
	DELPHYS BC	p. 82																		200 - 300 kVA 3/3

UPS - Transformer-based

	DELPHYS MP Elite+	p. 84																		80 - 200 kVA 3/3
--	--------------------------	-------	--	--	--	--	--	--	--	--	--	--	--	--	--	--	--	--	--	---------------------

AC/DC systems

	SHARYS IP enclosure	p. 56				15 - 100 A 24/48/110 VDC														
--	-------------------------------	-------	--	--	--	-----------------------------	--	--	--	--	--	--	--	--	--	--	--	--	--	--

Emergency CPSS

	MODULYS EM	p. 86				1.5 - 6 kVA 1/1														
	MASTERY EM	p. 86								10 - 20 kVA 3/1 & 3/3		30 - 80 kVA 3/3								
	DELPHYS EM	p. 86																		160 - 200 kVA 3/3