

Selection guide



Load break switches

UL products

Which application?



Which function?

Machine control	
	
SIRCO M UL 508	SIRCO M UL 98
16 to 80 A	30 to 100 A
<i>p. 2</i>	<i>p. 2</i>

Applications

Main switchboard	•	•
Distribution panel	•	•
Emergency load break	•	•
Genset output		•
Network coupling		•
Local safety load break	•	•
Machine control	•	•
Photovoltaic load break		
Enclosed switches	•	•
Surge protection		

Functions

3/4 pole load break switch	•	•
6/8 pole load break switch	•	
3/4 pole changeover switch (I-O-II)	•	
3/4 pole changeover switch (I-I+II-II)	•	

Characteristics

Operation

Manual (rotating)	•	•
Manual toggle	•	
Motorised		

Direct operation handle

Front	•	•
-------	---	---

External operation handle

Front	•	•
Right side	•	

Indication of breaking

Positive break indication	•	•
Visible contacts		

Switch body

Modular	•	•
---------	---	---

