



Selection guide

Fuse protection

Fuse protection

Application?

Type of operation?

Industry					
FUSERBLOC Front/side control 25 to 1250 A	FUSERBLOC Direct control 25 to 400 A	FUSOMAT SIDERMAT <i>fuse-combination</i> <i>switches</i> 250 to 1800 A	RM - RMS 32 to 125 A	Fuse bases 160 to 2500 A	gG and AM NFC/DIN 0.16 to 1250 A

Applications

Transformer output			•			•
Section connectors				•	•	•
Cabinet entrance	•	•	•			•
Wiring						•
Motor circuits	•	•	•			•
Semi-conductor protection				•	•	
Photovoltaic installations						

Device operation

Manual	•	•	•			
Via tripping			•			

Location of manual handle

Front		•	•			
Side		•	up to 1250 A			
Via a panel		up to 32 A				

Location of external handle

Front	•		•			
Right side	•		up to 1250 A			
Left side	Contact us					
Central	Contact us					

Breaking

Fully visible	•	•	•			
Visible			•			

Fuses

NFC/DIN	• / •	• / •	- / •	• / -	- / •	•
BS	see the UK catalogue	see the UK catalogue				•
UL	see UL catalogue	see UL catalogue				•
Other						

