



# TYPE APPROVAL CERTIFICATE



N. ELE095419CS

This is to certify that the product below is found to be in compliance with the applicable requirements of the RINA Type Approval System.

<b>Description</b>	<b>Fuse-Holder</b>
<b>Type</b>	<b>RM32, RM50, RM100</b>
<b>Applicant</b>	<b>SOCOMEK S.A.</b> 1 Rue De Westhouse BP 10 67 235 Benfeld France
<b>Manufacturer</b>	<b>DF S.A.</b> C/Silici, 67-69 08940 Cornellà De Llobregat, Barcelona Spain
<b>Testing Standards</b>	<b>Rules for the Classification of Ships –Part C – Machinery, Systems and Fire protection. Ch. 3, Sect. 6, Table 1</b>

Issued in **Genova** on **May 23, 2019**

This certificate is valid until **May 23, 2024**

*Valerio Bonanni*

RINA Services S.p.A.

*Valerio Bonanni*



## N. ELE095419CS

### Fuseholders for cylindrical Fuse-Links:

- Modular type
- Self-extinguishable materials
- DIN rail Mounting
- Rotating fuse carrier

Type	RM32	RM50	RM100
Version	Without indicator With indicator light	Without indicator With indicator light With microswitch	Without indicator With indicator light With microswitch
Poles	1P, 1P+N, 2P, 3P, 3P+N, 4P	1P, 1P+N, 2P, 3P, P+N, 4P	1P, 1P+N, 2P, 3P, 3P+N, 4P
Fuse-Link size	10x38	14x51	22x58
Rated voltage	690Vac (50Hz)	690Vac (50 Hz)	690Vac (50 Hz)
Rated current	32A (28,8A @ Tamb 45°C)	50A (45A @Tamb. 45°C)	100A (90A @Tamb. 45°C)
Rated insulation (V imp.)	6 kV	6 kV	6 kV
IP protection (IEC60529)	IP 20	IP 20	IP 20
Wire section	0,75... 25 mm <sup>2</sup> 0,75... 16 mm <sup>2</sup>	1,5...35 mm <sup>2</sup> 1,5...25 mm <sup>2</sup>	1,5...50 mm <sup>2</sup> 1,5...35 mm <sup>2</sup>

### Test reports:

Pierre SIAT Lab. \_ Vibration report n. FRM 12 62394  
 CB Test Certificates n. AT2983 (2014/02/11), AT2984 (2014/02/11), AT2985 (2014/02/11)

### Data sheet:

DF S.A. doc. on 01.40.0001E (2014/06/04)