





# Selection guide

## Current sensors and transformers

### ACCULine, RGW and CT 5A



Application	Measurement and metering			
	load current			
				
Models	<b>ROG-0</b>	<b>RGW-XXX</b>	<b>CT-0</b>	<b>5 A Current transformer</b>
Current type	AC	AC	AC	AC
Rated current range (A)	0 ... 10 000	0 ... 5 000	20 ... 4 000	5 ... 5 000
Window size (mm)	40 ... 1 000	40 ... 600	40 ... 120	14 ... 165
Product type	Split-core and flexible	Split-core and flexible	Split-core	Solid- and split-core
Standard	IEC 61869-10 UL 61010 UL 2808	IEC 61869-10	IEC 61869-2 UL 61010 UL 2808	IEC 61869-2
Accuracy class	1	1	0.2S ... 3	0.2S ... 1
Secondary signal	40 ... 333 mV/kA without integrator 333 mV with integration - integrable current range 200...5000 A	100 mV	100 ... 333 mV 1-5 A	5 A
Output type	Pre-wired Ferrule RJ12	Pre-wired	Pre-wired Terminal block RJ12	Terminal block
Customisable	•		•	



	Metering	Protection	Residual	
	for billing			
				
	<b>BCT-C</b>	<b>PCT-C</b>	<b>DCT-C</b>	<b>DCT-O</b>
	AC	AC	AC	AC
	100 ... 2 000	40 ... 4 000 A in rated current 120 kA in overload current	36 to 630 A per phase 3 mA to 30A of fault current	85 to 250 A per phase 3 mA to 30A of fault current
	40 ... 105	20 ... 105	15 ... 300	50 ... 120
	Solid-core	Solid-core	Solid-core	Split-core
	IEC 61869-2 IEC 61010	IEC 61869-2 IEC 61010	IEC 61869-1 UL 508 IEC 60947-2 Annex M IEC 62020	IEC 61869-1 UL 508 IEC 60947-2 Annex M IEC 62020
	0.2 ... 0.5S	5P5 ... 5P30	3	3
	5 A	1-5 A	10 ... 100 mV	10 ... 100 mV
	Terminal block	Terminal block	Pre-wired Terminal block Ferrule RJ12	Pre-wired Terminal block Ferrule RJ12
	•	•	•	•