

Selection guide




Load break switches

UL products

Which application?







Which function?

	Machine control		Power distribution	
				
	SIRCO M UL 508	SIRCO M UL 98	INOSYS LBS UL 98	
	16 to 80 A	30 to 100 A	100 to 1200 A	
	<i>p. 18</i>	<i>p. 18</i>	<i>p. 122</i>	
Applications				
Main switchboard	•	•	•	
Distribution panel	•	•	•	
Emergency load break	•	•	•	
Genset output		•		
Network coupling		•	•	
Local safety load break	•	•	•	
Machine control	•	•		
Photovoltaic load break				
Enclosed switches	•	•	•	
Surge protection				
Functions				
3/4 pole load break switch	•	•	•	
6/8 pole load break switch	•			
3/4 pole changeover switch (I-0-II)	•			
3/4 pole changeover switch (I-I+II-II)	•			
Characteristics				
Operation				
Manual (rotating)	•	•	•	
Manual toggle	•			
Motorised				
Direct operation handle				
Front	•	•	•	
External operation handle				
Front	•	•	•	
Right side	•		•	
Indication of breaking				
Positive break indication	•	•	•	
Visible contacts			•	
Switch body				
Modular	•	•	•	

Which operation handle?

Which type of breaking?

	Photovoltaic		DC and Photovoltaic	
				
	SIRCO MC PV UL 508I	SIRCO PV UL 98B	INOSYS LBS UL 98B	SIRCO MOT DC / DC ESS UL 98B
	25 to 40 A	100 to 2000 A	100 to 1200 A	2000 A
	<i>p. 62</i>	<i>p. 74</i>	<i>p. 122</i>	<i>p. 110</i>

				•
				•
		•	•	•
	•	•	•	•
	•	•	•	
	•	•	•	•
	•	•		

	•	•	•	•
				•
	•	•	•	•
	•	•	•	
	•	•	•	•
	•		•	