

Product Environmental Profile



ATyS Bypass Double Line 160 to 3200A

ATyS Bypass are enclosed transfer switches. Double line versions from 160A to 3200A are covered by this document.



The commitments of Socomec to respect the environment

As part of its environmental policy, Socomec is committed to:

- Incorporate the principles of the circular economy into the design of new products and services
- Promote longer product lifetimes
- Promote the use of environmentally responsible materials
- Design and develop solutions to further improve the energy efficiency of our products and services
- Inform our customers in a transparent manner about the environmental impact of our products throughout their life cycle.

To this end, Socomec is committed to constantly monitoring, anticipating and complying with environmental regulations as well as customer expectations relating to its products, and to ensuring that all those involved adhere to and take responsibility for its commitments.

Socomec is member of :



Member of WEEE Europe



PEP ecopassport® Registration number: SOCO-00101-V01.01-EN

SOCOME C S.A.S

Head office : 1, rue de Westhouse – F – B.P.60010 – 67235 Benfeld Cedex

Tél : 03 88 57 41 41 – Fax : 03 88 57 78 78 – www.socomec.com

Contact : http://www.socomec.com/contact-us_en.html

● Product information :

Reference product

The representative product is the ATyS Bypass 1600A Double Line with sales reference 17864160 with the following description: ATyS Bypass Double Line units provide automatic switchover to the available source in the event of electricity network failure.

Other covered references

This PEP covers other references listed in the table at the end of the document.

Functional unit

Ensure continuity of energy supply by transferring a load between two power supply sources for a rated current up to 3200A and rated voltage of 415VAC, for enclosure installation, in industrial applications areas, according to the appropriate use scenario, and during the reference life of 20 years of the product.

Enable bypass onto both sources, ensure continuity of service during maintenance and complete isolation of the automatic transfer switches for safe intervention without load interruption.

Ensure remote operation via motorised control.

● Materials and substances

Declaration of the constitutives materials

Total mass of the reference product (including packaging): 1013,15 kg among which packaging: 52 kg

For the reference product:

Plastics as % of weight		Metals as % of weight		Other as % of weight	
Polyester	8,85%	Steel	38,46%	Wood	4,95%
Polyamide	1,58%	Copper and its alloys	38,36%	Other inorganics	0,29%
PVC	1,54%	Zamak	2,16%	Other organics	0,17%
PUR	0,59%	Stainless steel	1,38%	Cardboard	<0,1%
ABS	0,46%	Aluminium and its alloys	0,52%	Paper	<0,1%
PC	0,43%	Nickel and its alloys	<0,1%	Electronic components	<0,1%
		Precious metals	<0,1%		
Other plastics	<0,1%				
Total Plastics: 136,18 kg	13,44%	Total Metals: 819,42 kg	80,88%	Total Others: 57,55 kg	5,68%

Substances management

Socomec is leading a program to limit the use of hazardous substances in the design of new products and to monitor the presence of substances of concern in its supplies to anticipate future use restrictions.



Directive 2011/65/EU : Product references covered by this PEP meet the requirements of the RoHS Directive on the restriction of substances such as lead, mercury, cadmium, hexavalent chromium, polybrominated biphenyl (PBB), polybrominated diphenyl ethers (PBDEs) and phthalates (DIBP, DEHP, BBP, DBP).



REACH 1907/2006 regulation: To the best of our knowledge, based on the supplier declarations, at the publication date of this document, the product do not contain any SVHC in a concentration above 0,1% per weight.

• Manufacturing



The products covered by this PEP are manufactured on the production site of Benfeld, France whose environmental management system has been ISO 14001 certified. Impacts on the environment are reduced by optimizing its energy consumption and by practicing a rigorous waste management.

• Distribution

As part of its distribution policy aiming to respect the environment, Socomec is in favor of groupage transports and ISO 14001 certified logistic partners.

No reconditioning is planned for the product. This phase is consequently neglected.

The sizing of the packaging has been optimized to ensure the best possible protection of the product at the lowest possible volume in order to reduce the impact of the transport stage on the environment.

• Installation

The installation phase consists in connecting the product to the existing electrical installation.

The installation does not generate any significant impacts on the environment, except impacts from packaging waste.

• Use phase

Use phase was modelised according to the following scenario:

Geography: European energy mix

Load rate: 100% of 1600A (In)

Reference Service Life: 20 years

Use scenario	Proportion of time spent [%]
Normal position	90,00%
Bypass position	9,00%
Test position	1,00%

Care and maintenance

The product does not require any maintenance under normal conditions of use.

Consumables

The product does not require consumables.


• End of life

End of life treatment

The following parts require specific care and selective treatment in accordance with Annex VII of the WEEE Directive 2012/19/EU - Waste of electrical and electronic equipment.

Maintenance and disassembly should always be conducted by qualified personnel.

Type of risk	Type of component	Location
Potential security hazard for operators	LCD screen	1
	Capacitors	2
Necessity of a selective treatment	LCD screen	1
	Capacitors	2
	Printed circuit boards	3
	Battery	4
	Fans	5



Recyclability potential of the product according to IEC TR 62635

The recyclability potential of the product is 75,07%.
This covers material and energy recovery potentials.

• Environmental impacts

Calculation methodology: life cycle assessment (LCA)



The calculation of the impacts on the environment was made using a life cycle assessment methodology in accordance with the ISO 14040 requirements and with PEP eco passport product category rules. For more details follow the link:

www.pep-ecopassport.org

This study was carried out with the following version of the software EIME and of the database:

EIME version: v6.2.1.

Database version: CODDE-2023-02

For biogenic carbon storage the following methodology was used : 0/0

PRODUCT ENVIRONMENTAL PROFILE

The whole life cycle has been taken into account:

Step	Geographical representativeness	Scenario
Manufacturing (M) (A1-A3)	Production of electronic components : Asia Production of other components and packaging : Europe Assembly : France	From the raw material extraction to the last Socomec logistic platform, including packaging Waste generated during manufacturing phase are taken into account.
Distribution (D) (A4)	Distribution scenario : Europe	From the last Socomec logistic platform to the final customer.
Installation (I) (A5)	Transport and treatment of packaging wastes : Local	Local road transport of 1000 km of generated wastes to the treatment site, end of life treatment.
Use phase (U) (B1-B7)	Energy mix : Europe	Power consumption required during 20 years and maintenance according to consumption scenario above mentioned.
End of life (EOL) (C1-C4)	Transport and treatment : Local	Road transport of 1000 km from the final customer to the treatment sites. End of life treatment.

Environmental impacts of the ATyS Bypass 1600A Double Line, per FU

The following impacts have been calculated to best represent geographically, temporally and technologically each step of the life cycle.

Indicators	Unit	Total impact	M (A1-A3)	D (A4)	I (A5)	U (B1-B7)	EOL (C1-C4)
Acidification	mol H+ eq.	2,28E+03	2,45E+02	2,26E+00	0*	2,03E+03	0*
Climate change - Total	kg CO2 eq.	3,64E+05	7,90E+03	3,58E+02	4,44E+01	3,56E+05	0*
Climate change - Biogenic	kg CO2 eq.	1,51E+03	1,03E+03	0*	0*	4,75E+02	0*
Climate change - Fossil	kg CO2 eq.	3,64E+05	8,49E+03	3,58E+02	8,16E+01	3,56E+05	0*
Climate change - Land use and land use transformation	kg CO2 eq.	9,49E-03	9,49E-03	0*	0*	0*	0*
Ecotoxicity, freshwater	CTUe	4,14E+06	3,10E+05	0*	0*	3,83E+06	0*
Particulate matter	disease occurrence	1,72E-02	1,48E-03	1,84E-05	0*	1,58E-02	0*
Eutrophication, freshwater	kg P eq.	9,93E-01	1,55E-02	1,34E-04	3,75E-04	9,75E-01	1,95E-03
Eutrophication, marine	kg N eq.	2,46E+02	1,43E+01	1,06E+00	3,46E-02	2,31E+02	2,33E-01
Eutrophication, terrestrial	mol N eq.	3,64E+03	1,58E+02	1,16E+01	3,66E-01	3,47E+03	2,55E+00
Human toxicity, cancer	CTUh	2,10E-02	2,10E-02	0*	0*	4,15E-05	0*
Human toxicity, non-cancer	CTUh	4,47E-03	2,82E-03	6,79E-07	0*	1,65E-03	0*
Ionising radiation, human health	kBq U235 eq.	8,38E+06	7,85E+06	0*	0*	5,29E+05	0*
Land use	No dimension	-2,20E+03	-9,28E+03	0*	0*	0*	0*
Ozone depletion	kg CFC-11 éq.	2,65E-03	1,10E-03	5,48E-07	0*	1,52E-03	2,48E-05
Photochemical ozone formation, human health	kg NMVOC eq.	7,91E+02	4,68E+01	2,93E+00	1,06E-01	7,41E+02	0*
Abiotic resource depletion - fossil fuels or resource depletion - fossils	MJ	9,36E+06	2,87E+05	4,98E+03	0*	9,07E+06	0*
Abiotic resource depletion - elements or resource depletion - metals and minerals	kg Sb eq.	1,61E+00	1,63E+00	0*	0*	2,58E-02	0*
Water use	m³ eq.	2,37E+04	1,08E+04	0*	3,82E+00	1,26E+04	2,26E+02
Net use of freshwater	m³	2,76E+02	1,26E+02	0*	4,45E-02	1,47E+02	2,64E+00
Total Primary Energy	MJ	5,55E+06	1,49E+05	2,50E+03	0*	5,41E+06	0*
Total use of non-renewable primary energy resources	MJ	4,68E+06	1,44E+05	2,49E+03	0*	4,54E+06	0*
Total use of renewable primary energy resources	MJ	8,76E+05	5,08E+03	0*	2,27E+02	8,71E+05	0*
Use of non renewable primary energy excluding non renewable primary energy used as raw material	MJ	4,67E+06	1,39E+05	2,49E+03	0*	4,54E+06	0*
Use of non renewable primary energy resources used as raw material	MJ	4,72E+03	4,72E+03	0*	0*	0*	0*
Use of non renewable secondary fuels	MJ	0,00E+00	0*	0*	0*	0*	0*
Use of renewable primary energy excluding renewable primary energy used as raw material	MJ	8,75E+05	3,68E+03	0*	2,27E+02	8,71E+05	0*
Use of renewable primary energy resources used as raw material	MJ	1,40E+03	1,40E+03	0*	0*	0*	0*
Use of renewable secondary fuels	MJ	0,00E+00	0*	0*	0*	0*	0*
Use of secondary material	kg	2,09E+02	2,09E+02	0*	0*	0*	0*
Hazardous waste disposed	kg	7,24E+04	6,95E+04	0*	0*	3,33E+03	0*
Non hazardous waste disposed	kg	2,49E+04	2,02E+02	6,27E+00	3,77E+01	2,56E+04	0*
Radioactive waste disposed	kg	6,18E+00	6,01E-01	4,47E-03	8,89E-04	5,36E+00	2,16E-01
Components for reuse	kg	0,00E+00	0*	0*	0*	0*	0*
Exported Energy	MJ	2,59E+01	9,33E+00	0*	1,65E+01	0*	0*

PRODUCT ENVIRONMENTAL PROFILE

Materials for energy recovery	kg	1,57E+01	0*	0*	1,57E+01	0*	0*
Materials for recycling	kg	1,55E+01	0*	0*	1,55E+01	0*	0*

Biogenic carbon content in the reference product:

Biogenic carbon content of the product	kg of C	0,00E+00	0*	N/A	N/A	N/A	N/A
Biogenic carbon content of the associated packaging	kg of C	2,03E+01	2,03E+01	N/A	N/A	N/A	N/A

NB : 0* means that this impact either represents less than 0.01% of the total life cycle of the reference flow, or has no impact (in the case where the total impact is zero).

For the use stage (U), the product does not require maintenance therefore the impacts values are representatives of the B6 phase from the use stage : "Energy requirements during the use stage"

Registration number : SOCO-00101-V01.01-EN	Drafting Rules : "PEP-PCR-ed4-EN 2021 09 06" Supplemented by : "PSR-0005-ed3.1-FR-2023 12 08"
Verifier accreditation number : VH46	Information and reference documents : www.pep-ecopassport.org
Date of issue: 07-2024	Validity period : 5 years
Independant verification of the declaration and data in compliance with ISO 14025 : 2006	
Internal : <input checked="" type="checkbox"/>	External : <input type="checkbox"/>
The PCR review was conducted by a panel of experts chaired by Julie Orgelet (DDemain) PEPs are compliant with XP C08-100-1 : 2016 or EN 50693:2019 The components of the present PEP may not be compared with components from any other program.	
Document complies with ISO 14025:2006 "Environmental labels and declarations. Type III environmental declarations"	



This document is intended to be only informative and non-contractual and does not create any right or obligation or commitment for Socomec towards its associates, customers or any other person or entity. All the values indicated in this document may change depending on many factors (use conditions, applications, installations, environment...). The life time mentioned in this document is only indicative and is not intended to be the minimal, maximal or average life time of the product.

Other references covered and extrapolation factors

For the products covered by the PEP other than the reference product, the environmental impacts of each phase of the lifecycle may be calculated with extrapolation factors following the proportionality rules that you can find below.

Extrapolation factors are determined as follows and can be provided upon request:

- For the Manufacturing and Distribution phases they are proportional to the mass of the product with its packaging;
- For the Installation phase they are proportional to the mass of the packaging;
- For the Use phase they are proportional to the power losses of the product;
- For the End of Life phase they are proportional to the mass of the product without its packaging.

Model	Reference
ATyS Bypass 1600A Double Line	17864160
ATyS Bypass 160A Double Line	17864016
ATyS Bypass 250A Double Line	17864025
ATyS Bypass 400A Double Line	17864040
ATyS Bypass 630A Double Line	17864063
ATyS Bypass 800A Double Line	17864080
ATyS Bypass 1000A Double Line	17864100
ATyS Bypass 1250A Double Line	17864120
ATyS Bypass 2000A Double Line	17864200
ATyS Bypass 2500A Double Line	17864250
ATyS Bypass 3200A Double Line	17864320