

# Product Environmental Profile



## Delphys Green Power 600 to 800 kVA

Uninterruptible power supply up to 800 kVA



### The commitments of Socomec to respect the environment

As part of its environmental policy, Socomec is committed to:

- Incorporate the principles of the circular economy into the design of new products and services
- Promote longer product lifetimes
- Promote the use of environmentally responsible materials
- Design and develop solutions to further improve the energy efficiency of our products and services
- Inform our customers in a transparent manner about the environmental impact of our products throughout their life cycle.

To this end, Socomec is committed to constantly monitoring, anticipating and complying with environmental regulations as well as customer expectations relating to its products, and to ensuring that all those involved adhere to and take responsibility for its commitments.

Socomec is member of :

**ecosystem**

Member of WEEE Europe



**Gimélec**

Environment and sustainable development commissions



PEP ecopassport® Registration number: SOCO-00084-V01.01-EN

SOCOME C S.A.S

Head office : 1, rue de Westhouse – F – B.P.60010 – 67235 Benfeld Cedex

Tél : 03 88 57 41 41 – Fax : 03 88 57 78 78 – [www.socomec.com](http://www.socomec.com)

Contact : [http://www.socomec.com/contact-us\\_en.html](http://www.socomec.com/contact-us_en.html)

**socomec**  
Innovative Power Solutions

● **Product information :**

Reference product	
Model	Delphys Green Power 800 kVA
Sales reference	1430803124
Description	Uninterruptible power supply up to 800 kVA
General data	
UPS Configuration	Single
UPS topology	Double conversion
UPS Performance classification	VFI-SS-111
Number of phases available	Three phase
Power [W]	800000
Apparent power [VA]	800000
Acoustic noise [dBA]	< 74 dBA
Efficiency	
Weighted UPS efficiency [%]	94,63%
Weight & dimensions	
Dimensions W*H*D [mm]	3510*2060*950
Mass without packaging [kg]	2797,8
Mass of the packaging [kg]	336

The UPS is not equipped with an energy storage system.

**Functional unit :**

To ensure the supply of power to remain within specified characteristics to equipment with load of 100 watts for a RSL of 1 years.

**Declared unit :**

To ensure the supply of power to remain within specified characteristics to equipment with load of 800000 watts for a RSL of 15 years.

*Mathematic relation between DU (declared unit) and FU (functional unit) mentioned in PSR-0010-ed2.0-EN 2023 12 08*

**References covered by this PEP with extrapolation rules:**

- Delphys Green Power 800 kVA with sales references: 1430803124; 1430802123; 1430802124; 1430802133; 1430802143; 1430803123; 1430803133; 1430803143; 1430804123; 1430804124; 1430804133; 1430805123; 1430805124; 1430805133

- Delphys Green Power 600 kVA with sales references: 1430600123; 1430600124; 1430600125; 1430600126; 1430600133; 1430600134; 1430600143

**Characteristics of the covered references:**

Model	Power [W]	Weighted UPS efficiency [%]	Product mass [kg]	Packaging mass [kg]
Declared Unit: Delphys Green Power 800 kVA	800000	94,63%	2798	336
Extrapolated unit: Delphys Green Power 600 kVA	600000	94,58%	2300	336

## • Materials and substances

### Declaration of the constitutives materials

Total mass of the Delphys Green Power 800 kVA (including packaging): 3133,8 kg among which packaging: 336 kg

For the reference product:

Plastics as % of weight		Metals as % of weight		Other as % of weight	
Polyester	2,37%	Stainless steel	24,38%	Electronic components	24,97%
Polyamide	0,70%	Copper and its alloys	17,45%	Wood	8,69%
PC	0,63%	Steel	12,57%	Cardboard	2,16%
PVC	0,56%	Aluminium and its alloys	3,55%	Other inorganics	0,46%
PE	0,21%	Nickel and its alloys	0,12%	Paper	<0,1%
ABS	0,14%	Other ferrous alloys	0,12%	Other organics	<0,1%
PBT	<0,1%	Zinc and its alloys	<0,1%		
Phenolic resin	<0,1%	Precious metals	<0,1%		
Epoxy resin	<0,1%	Tin and its alloys	<0,1%		
PTFE	<0,1%	Lead and its alloys	<0,1%		
		Other metals	<0,1%		
Other plastics	0,72%				
<b>Total Plastics: 169,47 kg</b>		<b>Total Metals: 1825,32 kg</b>		<b>Total Others: 1139,01 kg</b>	
<b>5,41%</b>		<b>58,25%</b>		<b>36,35%</b>	

### Substances management

Socomec is leading a program to limit the use of hazardous substances in the design of new products and to monitor the presence of substances of concern in its supplies to anticipate future use restrictions.



Directive 2011/65/EU : Product references covered by this PEP meet the requirements of the RoHS Directive on the restriction of substances such as lead, mercury, cadmium, hexavalent chromium, polybrominated biphenyl (PBB), polybrominated diphenyl ethers (PBDEs) and phthalates (DIBP, DEHP, BBP, DBP).



REACH 1907/2006 regulation: To the best of our knowledge, based on the supplier declarations, at the publication date of this document, the product do not contain any SVHC in a concentration above 0,1% per weight.

## • Manufacturing



The products covered by this PEP are manufactured on the production site of Huttenheim, France whose environmental management system has been ISO 14001 certified. Impacts on the environment are reduced by optimizing its energy consumption and by practicing a rigorous waste management.

## • Distribution

As part of its distribution policy aiming to respect the environment, Socomec is in favor of groupage transports and ISO 14001 certified logistic partners.

No reconditionning is planned for the product. This phase is consequently neglected.

The sizing of the packaging has been optimized to ensure the best possible protection of the product at the lowest possible volume in order to reduce the impact of the transport stage on the environment.

## ● Installation

The installation phase consists in connecting the product to the existing electrical installation.

The installation does not generate any significant impacts on the environment, except impacts from packaging waste.

## ● Use phase

### Consumption scenario

Use phase scenario: European energy mix

<b>Load (%)</b>	25%	50%	75%	100%
<b>Proportion of time spent (%)</b>	25%	50%	25%	0%

Total energy consumption during 15 years

<b>Total average energy consumption</b>	2726550 kWh
<b>Average UPS efficiency</b>	94,63%

### Care and maintenance

It is recommended to carry out periodic specialized maintenance in order to keep the equipment at the maximum level of efficiency and to avoid the installation being out of service with possible damage/risks.

Typical parts which are subjects to maintenance:

Components	DC capacitor filtering	AC capacitor filtering	Fans	Power supply PCB
<b>Number of replacement</b>	3	2	3	1

### Consumables


The product does not require consumables.

## ● End of life

### End of life treatment

The following parts require specific care and selective treatment in accordance with Annex VII of the WEEE Directive 2012/19/EU:

Waste of electrical and electronic equipment. Maintenance and disassembly should always be conducted by qualified personnel.



# PRODUCT ENVIRONMENTAL PROFILE

Type of component	Item	Part mass	Location
LCD	UNIP7-U4	0,750 kg	1
Condensateur	*	95,56 kg	2
Electronic cards	**	2,643 kg	3

\* : E136108, E136168, E136248, E136128, E136118

\*\* : S07078X01, E963367, S07002X02, E962697T, E963547, S07013X02, E961677, E961297, E960957, E961337, S07002X01, E961137, E961147, E961217, E960507, E963426, E964006, E961857T, E960857, E962597

## Recyclability potential of the product according to IEC TR 62635

The recyclability potential of the product is 76,9%.

This covers material and energy recovery potentials.

## • Additional information



This environmental declaration lists the information required in Annex A and B of IEC 62040-4 (Edition 1.0 2013-04) and EN 62040-4:2013 (2014-03).

## • Environmental impacts

### Calculation methodology: life cycle assessment (LCA)



The calculation of the impacts on the environment was made using a life cycle assessment methodology in accordance with the ISO 14040 requirements and with PEP eco passport product category rules.

For more details follow the link:

[www.pep-ecopassport.org](http://www.pep-ecopassport.org)

This study was carried out with the following version of the software EIME and of the database:

EIME version: v6.0.5

Database version: CODDE-2023-02

For biogenic carbon storage the following methodology was used : 0/0

The whole life cycle has been taken into account:

Step	Geographical representativeness	Scenario
<b>Manufacturing (M) (A1-A3)</b>	Production of electronic components : Asia Production of other components and packaging : Europe Assembly : France	From the raw material extraction to the last Socomec logistic platform, including packaging Waste generated during manufacturing phase are taken into account.
<b>Distribution (D) (A4)</b>	Distribution scenario : Europe	From the last Socomec logistic platform to the final customer. No product reconditioning.
<b>Installation (I) (A5)</b>	Transport and treatment of packaging wastes : Local	Local road transport of 1000 km of generated wastes to the treatment site, end of life treatment.
<b>Use phase (U) (B1-B7)</b>	Energy mix : Europe Production of maintenance components: analog to manufacturing phase	Power consumption required during 15 years according to consumption scenario above mentioned.
<b>End of life (EOL) (C1-C4)</b>	Transport and treatment : Local	Road transport of 1000 km from the final customer to the treatment sites. End of life treatment.

## Environmental impacts of the Delphys Green Power 800 kVA per functional unit (power of 100W and a lifespan of 1 year)

The following impacts have been calculated to best represent geographically, temporally and technologically each step of the life cycle.

Indicators	Unit	Total impact	M (A1-A3)	D (A4)	I (A5)	U (B1-B7)	EOL (C1-C4)
Acidification	mol H+ eq.	5,59E-02	2,51E-03	2,92E-05	0*	5,34E-02	1,08E-05
Climate change - Total	kg CO2 eq.	9,53E+00	1,76E-01	4,61E-03	0*	9,34E+00	2,06E-03
Climate change - Biogenic	kg CO2 eq.	1,83E-02	5,37E-03	0*	2,77E-05	1,29E-02	0*
Climate change - Fossil	kg CO2 eq.	9,51E+00	1,71E-01	4,61E-03	0*	9,33E+00	2,06E-03
Climate change - Land use and land use transformation	kg CO2 eq.	3,16E-07	3,15E-07	0*	0*	1,01E-09	0*
Ecotoxicity, freshwater	CTUe	1,10E+02	8,18E+00	0*	1,61E-02	1,01E+02	1,37E-02
Particulate matter	disease occurrence	4,31E-07	1,58E-08	2,37E-10	0*	4,14E-07	8,02E-11
Eutrophication, freshwater	kg P eq.	2,67E-05	6,63E-07	0*	8,56E-09	2,57E-05	3,06E-07
Eutrophication, marine	kg N eq.	6,29E-03	2,08E-04	1,37E-05	1,46E-06	6,06E-03	4,59E-06
Eutrophication, terrestrial	mol N eq.	9,40E-02	2,52E-03	1,50E-04	1,28E-05	9,13E-02	4,75E-05
Human toxicity, cancer	CTUh	1,84E-06	1,84E-06	0*	0*	5,44E-09	0*
Human toxicity, non-cancer	CTUh	6,67E-08	2,28E-08	8,76E-12	6,88E-12	4,39E-08	0*
Ionising radiation, human health	kBq U235 eq.	4,19E+01	2,79E+01	0*	0*	1,39E+01	0*
Land use	No dimension	1,88E-01	2,39E-03	0*	0*	1,86E-01	0*
Ozone depletion	kg CFC-11 éq.	6,67E-08	1,96E-08	7,06E-12	1,01E-11	4,71E-08	2,54E-11
Photochemical ozone formation, human health	kg NMVOC eq.	2,04E-02	8,01E-04	3,78E-05	3,06E-06	1,95E-02	1,23E-05
Abiotic resource depletion - fossil fuels or resource depletion - fossils	MJ	2,44E+02	6,18E+00	6,42E-02	0*	2,38E+02	2,85E-02
Abiotic resource depletion - elements or resource depletion - metals and minerals	kg Sb eq.	2,82E-05	2,37E-05	0*	0*	4,48E-06	0*
Water use	m³ eq.	-1,28E+00	-1,63E+00	0*	0*	0*	0*
Net use of freshwater	m³	-2,97E-02	-3,79E-02	0*	0*	0*	0*
Total Primary Energy	MJ	2,90E+02	6,33E+00	6,43E-02	0*	2,83E+02	0*
Total use of non-renewable primary energy resources	MJ	2,44E+02	6,18E+00	6,42E-02	0*	2,38E+02	2,85E-02
Total use of renewable primary energy resources	MJ	4,58E+01	1,55E-01	0*	1,13E-02	4,56E+01	0*
Use of non renewable primary energy excluding non renewable primary energy used as raw material	MJ	2,44E+02	6,10E+00	6,42E-02	0*	2,38E+02	2,85E-02
Use of non renewable primary energy resources used as raw material	MJ	9,85E-02	8,25E-02	0*	0*	1,60E-02	0*
Use of non renewable secondary fuels	MJ	0,00E+00	0*	0*	0*	0*	0*
Use of renewable primary energy excluding renewable primary energy used as raw material	MJ	4,57E+01	7,73E-02	0*	1,13E-02	4,56E+01	0*
Use of renewable primary energy resources used as raw material	MJ	8,05E-02	7,82E-02	0*	0*	2,35E-03	0*
Use of renewable secondary fuels	MJ	0,00E+00	0*	0*	0*	0*	0*
Use of secondary material	kg	1,43E-05	1,37E-05	0*	0*	5,62E-07	0*
Hazardous waste disposed	kg	1,33E+00	1,07E+00	0*	0*	2,59E-01	0*
Non hazardous waste disposed	kg	1,50E+00	1,02E-01	1,62E-04	1,78E-03	1,37E+00	2,32E-02
Radioactive waste disposed	kg	4,89E-04	1,31E-04	1,15E-07	0*	3,57E-04	4,14E-07
Components for reuse	kg	0,00E+00	0*	0*	0*	0*	0*
Exported Energy	MJ	8,40E-04	8,40E-04	0*	0*	0*	0*

Materials for energy recovery	kg	1,62E-03	0*	0*	1,62E-03	0*	0*
Materials for recycling	kg	7,35E-04	3,03E-06	0*	7,29E-04	2,92E-06	0*

Biogenic carbon content in the reference product:

Biogenic carbon content of the product	kg of C	0,00E+00	0*	N/A	N/A	N/A	N/A
Biogenic carbon content of the associated packaging	kg of C	1,25E+02	1,25E+02	N/A	N/A	N/A	N/A

NB : 0\* means that this impact either represents less than 0.01% of the total life cycle of the reference flow, or has no impact (in the case where the total impact is zero).

The aforementioned impacts (except for the biogenic carbon content) are declared for the functional unit of the reference product.

The environmental impacts of the reference product per declared unit can be calculated by multiplying the values of the environmental indicators by the factor available in the following table.

Life cycle phase	All life cycle phase
Factor	120000

### Other covered references

For the products covered by the PEP other than the reference product, the environmental impacts of each phase of the lifecycle are calculated by multiplying the declared unit impacts values with the following extrapolation factors:

Model	M (A1-A3)	D (A4)	I (A5)	U (B1-B7)	EOL (C1-C4)
Delphys Green Power 800 kVA	1,00	1,00	1,00	1,00	1,00
Delphys Green Power 600 kVA	0,84	0,84	1,00	0,76	0,82

Registration number : SOCO-00084-V01.01-EN	Drafting Rules : "PEP-PCR-ed4-EN 2021 09 06" Supplemented by : "PSR-0010-ed2.0-EN 2023 12 08"	
Verifier accreditation number : VH12	Information and reference documents : <a href="http://www.pep-ecopassport.org">www.pep-ecopassport.org</a>	
Date of issue: 01-2024	Validity period : 5 years	
Independant verification of the declaration and data, in compliance with ISO 14025 : 2006		
Internal : <input checked="" type="checkbox"/> External : <input type="checkbox"/>		
The PCR review was conducted by a panel of experts chaired by Julie Orgelet (DDemain)		
PEPs are compliant with XP C08-100-1 : 2016 or EN 50693:2019		
The components of the present PEP may not be compared with components from any other program.		
Document complies with ISO 14025:2006 "Environmental labels and declarations. Type III environmental declarations"		

*This document is intended to be only informative and non-contractual and does not create any right or obligation or commitment for Socomec towards its associates, customers or any other person or entity. All the values indicated in this document may change depending on many factors (use conditions, applications, installations, environment...). The life time mentioned in this document is only indicative and is not intended to be the minimal, maximal or average life time of the product.*